

## Odyssey PC Specifications for Windows®-Based Workstations

The following is recommended PC hardware, software and network specifications for deployment of Odyssey Assistant software.

### PC Hardware / Settings

Manufacturer / Model	No Preference
Processor*	2.0GHz Core Duo™, or better
Memory (RAM)	2 GB or better
Virtual Memory Paging File	3x physical memory
Disk Space**	80MB free disk space

*\*Users that access more than one site (production, test, conversion, etc) will require an additional 45 MB of free disk space for each additional site.*

*\*\*The Odyssey Assistant window requires 4:3 aspect ratio for optimal display.*

### PC Software

Operating System*	Windows 7 Pro or Windows 8 Pro
Web Browser**	Internet Explorer® 8, 9 or 10
Word Processor**	MS Word® 2007, 2010 or 2013

*\* Users require local PC admin rights. UAC must be turned off and Windows 8.1 is currently unsupported.*

*\*\*Web browser required for basic Odyssey functionality; word processor required for forms processing.*

### Form/Report/Document Printers

1. Windows compliant laser printers for 8 ½" x 11" paper

*\*HP LaserJet printers are recommended*

### Case Label Printers (Roll-feed 4" x 3")

1. Zebra TLP 3844-Z Parallel, USB connection
2. Zebra TLP 2844-Z Parallel, USB connection
3. Zebra TLP 2824 Plus
4. Zebra GK420t
5. Zebra GK430t
6. Dymo LabelWriter 450, USB connection

### Receipt Printers (Roll-feed)

1. Epson TM-U375 Parallel or USB connection
2. Epson TM-U220 Parallel or USB connection

*\*Odyssey support is limited to the exact model(s) specified. Ethernet connection is not supported.*