

## Odyssey PC Specifications for Windows®-Based Workstations

The following is recommended PC hardware, software and network specifications for deployment of Odyssey Assistant software.

### PC Hardware / Settings

Manufacturer / Model	No Preference
Processor*	Intel Core i5 at 3GHz (desktop) and 2.3 GHz (laptop)
Memory (RAM)	4 GB or better, preferred is 8GB
Virtual Memory Paging File	3x physical memory
Disk Space**	80MB free disk space

*\*Users that access more than one site (production, test, conversion, etc) will require an additional 45 MB of free disk space for each additional site.*

*\*\*The Odyssey Assistant window requires 4:3 aspect ratio for optimal display.*

*\*\*\* Once the computer is set up in the county, it needs to be set for High Performance power mode, however sleep and turn off display settings can still be used. Using High Performance mode keeps the CPU at its rated speed which will result in much better Odyssey performance for the end user.*

### PC Software

Operating System*	Windows 7 Pro 64 bit or higher
Web Browser**	Internet Explorer® 8, 9 or 10
Word Processor**	MS Word® 2007, 2010 or 2013

*\* Users require local PC admin rights. UAC must be turned off and Windows 8.1 is currently unsupported.*

*\*\*Web browser required for basic Odyssey functionality; word processor required for forms processing.*

### Form/Report/Document Printers

1. Windows compliant laser printers for 8 ½" x 11" paper

*\*HP LaserJet printers are recommended*

### Case Label Printers (Roll-feed 4" x 3")

1. Zebra TLP 3844-Z Parallel, USB connection
2. Zebra TLP 2844-Z Parallel, USB connection
3. Zebra TLP 2824 Plus
4. Zebra GK420t
5. Zebra GK430t
6. Dymo LabelWriter 450, USB connection

### Receipt Printers (Roll-feed)

1. Epson TM-U375 Parallel or USB connection
2. Epson TM-U220 Parallel or USB connection

*\*Odyssey support is limited to the exact model(s) specified. Ethernet connection is not supported.*